

CC-E

Immersion Thermostat with Plug & Play Technology. Powerful pressure and suction pump made of high-resistant plastic. Moistened parts in stainless steel or high-resistant plastics. With adjustable overtemperature protection according to DIN 12876.

Pilot ONF:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-2 warranty - registration required.

Technical data according to DIN 12876

25...200 °C Operating temperature range with water cooling 20...200 °C with refrigerator -30...200 °C Temperature stability at 70°C 0.01 K temperature set point / display Absolute accuracy Internal temperature sensor Pt100 Sensor external connection Pt100 Interface digital Safety classification Heating power at 240V

Heating power at 240V
Heating power at 230V
Heating power at 220V
Heating power at 208V
Heating power at 200V
Pressure pump
max. delivery
max. delivery pressure
Suction pump
max. delivery pressure (suction)

max. delivery pressure (suction) Pump connenction (optional) Immersion depth

Overall dimensions WxDxH **

Net weight

Power supply requirement

Power input
max. current
min. Fuse
max. Fuse
Degree of Protection
min. ambient temperature
max. ambient temperature

5,7" colour Touchscreen setup for calibration Ethernet, USB (Host u. Device), RS232 Class III / FL 2.1 kW 2 kW 1,8 kW 1,6 kW 1,5 kW ves 27 I/min 0.7 bar ves 22 I/min 0.4 bar M16x1 male 150 mm 132x159x315 mm 4 kg

200-240V 1~/2~ 50/60Hz

Order-No.: 2000.0023.01



2,1 kW

10 A

10A 16A

IP20

5°C

40 °C

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original. Accessories and periphery: mini-USB cable #54949*, screw clamp #30541*, cooling coil #30554, dummy plugs, sleeve nuts thread M16x1, pump adaptor #19606, Note: When using Huber pump adapter: Polyglycol is not permissible to be used as a heat transfer fluid,hose connector NW12 #6087, connection tubes, waterbaths in polycarbonat and stainless steel * standard equipment

Output data valid for: Room temperature 20°C

In accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction.

Example: -10% voltage and +3% frequency -> not allowed!

-10% voltage and -3% frequency -> allowed.

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

- 1. Single-phase devices (230V/115V) -> with cable and plug
- 2. Three-phase devices with current consumption less than 63A -> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A -> without cable, without plug
- ** Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau AG Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com