

## TI-H-5

### Multi-frequency ultrasonic cleaning unit

#### Elma Order Nos

TI-H-5 MF2 230V	239 010 0020
TI-H-5 MF2 115V	239 010 0023
TI-H-5 MF2 100V	239 010 0024
TI-H-5 MF3 230V	239 010 0010
TI-H-5 MF3 115V	239 010 0013
TI-H-5 MF3 100V	239 010 0014
Stainless steel Cover	239 010 0050
Stainless steel basket 200 / 100 / 90 mm	200 000 0995
Hinged cover for heat and sound insulation	239 015 0000



Pictured TI-H-5

Powerful cleaning unit of robust quality, with ergonomic design and innovative technology:

- two selectable frequencies on MF2 and MF3 models for intensive and gentle cleaning
- available frequency pairs 25/45kHz, 35/130kHz or single-frequency 35kHz
- multi-frequency model with 25/45 kHz:
  - 25 kHz for the coarse cleaning and removal of lapping and polishing media
  - 45 kHz for the fine cleaning and removal of oil and grease
  - ideal for hard surfaces made of metal and glass in the industrial, craft and jewellery manufacturing sector, only suitable for hard precious stones
- multi-frequency model with 35/130 kHz:
  - 35 kHz for the removal of oil and grease from hard surfaces, such as metal, glass and hard precious stones
  - 130 kHz for the cleaning of sensitive surfaces in the jewellery or electronics business
- Degas mode for the efficient degassing of the cleaning liquid
- Sweep mode for the perfect sound field distribution
- variable ultrasonic power
- transducer tanks made of special stainless steel, for powerful use and a long service life of the transducer tank
- timer for ultrasonic activity, variable between 0 and 15 min. and permanent operation
- temperature control 30 - 80 °C

#### Technical data

Mains voltage (Vac)	100-120V oder 230V	Tank capacity (litres)	3,5
Mains connection	1Ph. / 1N / 1 PE	Weight (kg)	10,5
Power consumption total (W)	500	Drain	1/2"
Ultrasonic power effective (W)	100	Material tank	Stainless steel
Ultrasonic peak performance max.* (W)	400	Material casing	Stainless steel
Heating (W)	400	Protection class	IP 21
Unit outer dimensions W / D / H (mm)	340 / 300 / 370**		
Tank internal dimensions W / D / H (mm)	240 / 130 / 150		

\* The signal form of the wave results in a factor 4 for the ultrasonic peak max., depending on the modulation of the wave.